

Eaton UTS712D3S

Plastic jam nut receptacle, without backshell, with 3 female PCB contacts, IP68/69K in unmated conditions; UTS712D3S

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS712D3S
PRODUCT LENGTH/DEPTH	25.3 mm
PRODUCT HEIGHT	31.8 mm
PRODUCT WIDTH	31.8 mm
PRODUCT WEIGHT	16.2 g
COMPLIANCES	CSA-C22.2 No.182.3 (please contact us for more details) UL 1977 (please contact us for more details) IEC 61984 (please contact us for more details) ROHS exemption 6.c

CURRENT RATING	16 A IEC 13 A UL
ENVIRONMENTAL CONDITIONS	Flammability rating UL94 HB REACH RoHS
ENVIRONMENTAL RESISTANCE	Resistant against basic bath Resistant against gasoline Resistant against mineral oil Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against acid bath Resistant against oil UV resistant, no degradation after 5 years of exposure in natural environment
TEST CURRENT	13 A CSA 16 A IEC 13 A UL
TEST VOLTAGE	150 V IEC 600 V CSA 600 V UL
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold
CONTACT TYPE	PCB
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	3
SHELL MATERIAL	Plastic
SHELL SIZE	12
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C



RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	3
NUMBER OF CAVITY #16	3
NUT MATERIAL	Aluminium
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: