

Eaton UTS712D3SY

Plastic jam nut receptacle, without backshell, with 3 female PCB contacts, IP68/69K in unmated conditions, keying Y; UTS712D3SY

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS712D3SY
PRODUCT LENGTH/DEPTH	25.3 mm
PRODUCT HEIGHT	31.8 mm
PRODUCT WIDTH	31.8 mm
PRODUCT WEIGHT	16.2 g
COMPLIANCES	CSA-C22.2 No.182.3 (please contact us for more details) IEC 61984 (please contact us for more details) UL 1977 (please contact us for more details) ROHS exemption 6.c

CURRENT RATING	16 A IEC 13 A UL
ENVIRONMENTAL CONDITIONS	RoHS Flammability rating UL94 HB REACH
ENVIRONMENTAL RESISTANCE	Resistant against oil Resistant against gasoline Resistant against basic bath Resistant against acid bath
	UV resistant, no degradation after 5 years of exposure in natural environment Resistant against mineral oil Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz
TEST CURRENT	13 A UL 16 A IEC 13 A CSA
TEST VOLTAGE	150 V IEC 600 V UL 600 V CSA
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	Y
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold
CONTACT TYPE	PCB
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	3
SHELL MATERIAL	Plastic
SHELL SIZE	12
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C



RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	3
NUMBER OF CAVITY #16	3
NUT MATERIAL	Aluminium
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

