

Eaton UTS712D8PZ32

Plastic jam nut receptacle & hold down clips, without backshell, with 8 male PCB contacts, IP68/69K in unmated conditions, keying Z; UTS712D8PZ32

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS712D8PZ32
PRODUCT LENGTH/DEPTH	25.3 mm
PRODUCT HEIGHT	31.8 mm
PRODUCT WIDTH	31.8 mm
PRODUCT WEIGHT	15.1 g
COMPLIANCES	CSA-C22.2 No.182.3 (please contact us for more details) IEC 61984 (please contact us for more details) ROHS exemption 6.c UL 1977 (please contact us for more details)

CURRENT RATING	4.5 A UL 6 A IEC
ENVIRONMENTAL CONDITIONS	Flammability rating UL94 HB RoHS REACH
ENVIRONMENTAL RESISTANCE	Resistant against mineral oil Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against oil Resistant against gasoline Resistant against basic bath Resistant against acid bath UV resistant, no degradation after 5 years of exposure in natural environment
TEST CURRENT	4.5 A UL 6 A IEC 4.5 A CSA
TEST VOLTAGE	250 V UL 32 V IEC 250 V CSA
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	Z
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Pin (Male)
CONTACT PLATING	Gold
CONTACT TYPE	PCB
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
SHELL MATERIAL	Plastic
SHELL SIZE	12
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Jam Nut Receptacle



NUMBER OF CONTACTS	8
NUMBER OF CAVITY #20	8
NUT MATERIAL	Aluminium
SALT SPRAY	500 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

