

Eaton UTS712D8SW

Plastic jam nut receptacle, without backshell, with 8 female PCB contacts, IP68/69K in unmated conditions, keying W; UTS712D8SW

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS712D8SW
PRODUCT LENGTH/DEPTH	25.3 mm
PRODUCT HEIGHT	31.8 mm
PRODUCT WIDTH	31.8 mm
PRODUCT WEIGHT	16.8 g
COMPLIANCES	ROHS exemption 6.c UL 1977 (please contact us for more details) CSA-C22.2 No.182.3 (please contact us for more details) IEC 61984 (please contact us for more details)

CURRENT RATING	4.5 A UL 6 A IEC
ENVIRONMENTAL CONDITIONS	RoHS Flammability rating UL94 HB REACH
ENVIRONMENTAL RESISTANCE	Resistant against acid bath
	Resistant against oil Resistant against mineral oil Resistant against basic bath Resistant against gasoline Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz UV resistant, no degradation after 5 years of exposure in natural environment
TEST CURRENT	4.5 A UL 6 A IEC 4.5 A CSA
TEST VOLTAGE	250 V CSA 32 V IEC 250 V UL
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	W
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold
CONTACT TYPE	PCB
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
SHELL MATERIAL	Plastic
SHELL SIZE	12
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Jam Nut Receptacle

NUMBER OF CONTACTS	8
NUMBER OF CAVITY #20	8
NUT MATERIAL	Aluminium
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

