

## Eaton UTS712D8SY32

Plastic jam nut receptacle & hold down clips, without backshell, with 8 female PCB contacts, IP68/69K in unmated conditions, keying Y; UTS712D8SY32

<b>PRODUCT NAME</b>	Eaton Souriau UTS series plastic waterproof IP68/69k connector
<b>CATALOG NUMBER</b>	UTS712D8SY32
<b>PRODUCT LENGTH/DEPTH</b>	25.3 mm
<b>PRODUCT HEIGHT</b>	31.8 mm
<b>PRODUCT WIDTH</b>	31.8 mm
<b>PRODUCT WEIGHT</b>	16.8 g
<b>COMPLIANCES</b>	CSA-C22.2 No.182.3 (please contact us for more details) IEC 61984 (please contact us for more details) ROHS exemption 6.c UL 1977 (please contact us for more details)

CURRENT RATING	6 A IEC 4.5 A UL
ENVIRONMENTAL CONDITIONS	REACH Flammability rating UL94 HB RoHS
ENVIRONMENTAL RESISTANCE	Resistant against mineral oil Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against basic bath Resistant against gasoline Resistant against acid bath  UV resistant, no degradation after 5 years of exposure in natural environment Resistant against oil
TEST CURRENT	4.5 A UL 4.5 A CSA 6 A IEC
TEST VOLTAGE	250 V UL 250 V CSA 32 V IEC
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	Y
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold
CONTACT TYPE	PCB
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
SHELL MATERIAL	Plastic
SHELL SIZE	12
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Jam Nut Receptacle



NUMBER OF CONTACTS	8
NUMBER OF CAVITY #20	8
NUT MATERIAL	Aluminium
SALT SPRAY	500 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

