

Eaton UTS712E10PY

Plastic jam nut receptacle, without backshell, with 10 male solder contacts, IP68/69K in unmated conditions, keying Y; UTS712E10PY

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS712E10PY
PRODUCT LENGTH/DEPTH	25.3 mm
PRODUCT HEIGHT	31.8 mm
PRODUCT WIDTH	31.8 mm
PRODUCT WEIGHT	15.3 g
COMPLIANCES	IEC 61984 (please contact us for more details) CSA-C22.2 No.182.3 (please contact us for more details) UL 1977 (please contact us for more details) ROHS exemption 6.c

CURRENT RATING	16 A IEC 10 A UL
ENVIRONMENTAL CONDITIONS	REACH Flammability rating UL94 HB RoHS
ENVIRONMENTAL RESISTANCE	UV resistant, no degradation after 5 years of exposure in natural environment Resistant against acid bath
	Resistant against mineral oil Resistant against gasoline Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against oil Resistant against basic bath
TEST CURRENT	16 A IEC 10 A UL 7 A CSA
TEST VOLTAGE	500 V CSA 300 V IEC 500 V UL
CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
CONNECTOR ORIENTATION	Y
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Pin (Male)
CONTACT PLATING	Gold
CONTACT TYPE	Solder Cup
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	10
SHELL MATERIAL	Plastic
SHELL SIZE	12
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C

RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	10
NUMBER OF CAVITY #20	10
NUT MATERIAL	Aluminium
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: