



Eaton UTS712E8SZ

Plastic jam nut receptacle, without backshell, with 8 female solder contacts, IP68/69K in unmated conditions, keying Z; UTS712E8SZ

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS712E8SZ
PRODUCT LENGTH/DEPTH	25.3 mm
PRODUCT HEIGHT	31.8 mm
PRODUCT WIDTH	31.8 mm
PRODUCT WEIGHT	16.1 g
COMPLIANCES	IEC 61984 (please contact us for more details) UL 1977 (please contact us for more details) ROHS exemption 6.c CSA-C22.2 No.182.3 (please contact us for more details)



CURRENT RATING	4.5 A UL 6 A IEC
ENVIRONMENTAL CONDITIONS	REACH RoHS Flammability rating UL94 HB
ENVIRONMENTAL RESISTANCE	Resistant against gasoline Resistant against basic bath Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz UV resistant, no degradation after 5 years of exposure in natural environment Resistant against mineral oil Resistant against acid bath Resistant against oil
TEST CURRENT	4.5 A UL 6 A IEC 4.5 A CSA
TEST VOLTAGE	32 V IEC 250 V CSA 250 V UL
CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
CONNECTOR ORIENTATION	Z
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold
CONTACT TYPE	Solder Cup
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
SHELL MATERIAL	Plastic
SHELL SIZE	12
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Jam Nut Receptacle



NUMBER OF CONTACTS	8
NUMBER OF CAVITY #16	8
NUMBER OF CAVITY #20	8
NUT MATERIAL	Aluminium
SALT SPRAY	500 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

