

Eaton UTS71492SY

Plastic jam nut receptacle, without backshell, for 12 female contacts, IP68/69K, keying Y; UTS71492SY

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS71492SY
PRODUCT LENGTH/DEPTH	33.9 mm
PRODUCT HEIGHT	34.9 mm
PRODUCT WIDTH	34.9 mm
PRODUCT WEIGHT	8.9 g
COMPLIANCES	IEC 61984 (please contact us for more details) CSA-C22.2 No.182.3 (please contact us for more details) UL 1977 (please contact us for more details)



CURRENT RATING	10 A IEC 10 A UL
ENVIRONMENTAL CONDITIONS	REACH Fire and smoke rating I2F3 according to NFF 16101 and NFF 16102 Fire & Smoke Flammability rating UL94 V0 RoHS
ENVIRONMENTAL RESISTANCE	Resistant against mineral oil Resistant against basic bath Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz UV resistant, no degradation after 5 years of exposure in natural environment Resistant against gasoline Resistant against acid bath Resistant against oil
TEST CURRENT	10 A UL 10 A IEC 7 A CSA
TEST VOLTAGE	600 V CSA 63 V IEC 600 V UL
CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
CONNECTOR ORIENTATION	Y
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Polyamide
LAYOUT	92
SHELL MATERIAL	Plastic
SHELL SIZE	14
MATING CYCLES	250
OPERATING	105 °C

TEMPERATURE - MAX	
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	12
NUMBER OF CAVITY #16	12
NUT MATERIAL	Aluminium
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

