

# Eaton UTS714D15PY

Plastic jam nut receptacle, without backshell, with 15 male PCB contacts, IP68/69K in unmated conditions, keying Y; UTS714D15PY

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS714D15PY
PRODUCT LENGTH/DEPTH	25.3 mm
PRODUCT HEIGHT	34.9 mm
PRODUCT WIDTH	34.9 mm
PRODUCT WEIGHT	24.8 g
COMPLIANCES	UL 1977 (please contact us for more details) ROHS exemption 6.c CSA-C22.2 No.182.3 (please contact us for more details) IEC 61984 (please contact us for more details)

CURRENT RATING	4 A IEC 12 A UL
ENVIRONMENTAL CONDITIONS	Flammability rating UL94 HB REACH RoHS
ENVIRONMENTAL RESISTANCE	Resistant against gasoline UV resistant, no degradation after 5 years of exposure in natural environment Resistant against mineral oil Resistant against basic bath Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against acid bath  Resistant against oil
TEST CURRENT	12 A UL 4 A IEC 12 A CSA
TEST VOLTAGE	50 V IEC 600 V UL 600 V CSA
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	Y
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Pin (Male)
CONTACT PLATING	Gold
CONTACT TYPE	PCB
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	15
SHELL MATERIAL	Plastic
SHELL SIZE	14
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C



RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	15
NUMBER OF CAVITY #16	1
NUMBER OF CAVITY #20	14
NUT MATERIAL	Aluminium
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com  
© 2025

Follow us on social media to get the latest product and support information.

