

# Eaton UTS714D15SW

Plastic jam nut receptacle, without backshell, with 15 female PCB contacts, IP68/69K in unmated conditions, keying W; UTS714D15SW

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS714D15SW
PRODUCT LENGTH/DEPTH	25.3 mm
PRODUCT HEIGHT	34.9 mm
PRODUCT WIDTH	34.9 mm
PRODUCT WEIGHT	26.8 g
COMPLIANCES	CSA-C22.2 No.182.3 (please contact us for more details) UL 1977 (please contact us for more details) IEC 61984 (please contact us for more details) ROHS exemption 6.c

CURRENT RATING	12 A UL 4 A IEC
ENVIRONMENTAL CONDITIONS	REACH Flammability rating UL94 HB RoHS
ENVIRONMENTAL RESISTANCE	Resistant against gasoline Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against oil Resistant against basic bath Resistant against mineral oil UV resistant, no degradation after 5 years of exposure in natural environment Resistant against acid bath
TEST CURRENT	4 A IEC 12 A CSA 12 A UL
TEST VOLTAGE	50 V IEC 600 V CSA 600 V UL
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	W
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold
CONTACT TYPE	PCB
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	15
SHELL MATERIAL	Plastic
SHELL SIZE	14
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C



RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	15
NUMBER OF CAVITY #16	1
NUMBER OF CAVITY #20	14
NUT MATERIAL	Aluminium
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

