

Eaton UTS714D18SW32

Plastic jam nut receptacle & hold down clips,without backshell, with 18 female PCB contacts, IP68/69K in unmated conditions, keying W; UTS714D18SW32

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS714D18SW32
PRODUCT LENGTH/DEPTH	25.3 mm
PRODUCT HEIGHT	34.9 mm
PRODUCT WIDTH	34.9 mm
PRODUCT WEIGHT	23.9 g
COMPLIANCES	CSA-C22.2 No.182.3 (please contact us for more details) IEC 61984 (please contact us for more details) UL 1977 (please contact us for more details) ROHS exemption 6.c

CURRENT RATING	5 A IEC 4 A UL
ENVIRONMENTAL CONDITIONS	RoHS Flammability rating UL94 HB REACH
ENVIRONMENTAL RESISTANCE	Resistant against gasoline Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz UV resistant, no degradation after 5 years of exposure in natural environment Resistant against mineral oil Resistant against basic bath Resistant against oil Resistant against acid bath
TEST CURRENT	4 A UL 4 A CSA 5 A IEC
TEST VOLTAGE	250 V UL 50 V IEC 250 V CSA
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	W
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold
CONTACT TYPE	PCB
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	18
SHELL MATERIAL	Plastic
SHELL SIZE	14
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C



RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	18
NUMBER OF CAVITY #20	18
NUT MATERIAL	Aluminium
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: