

Eaton UTS714E15SY

Plastic jam nut receptacle, without backshell, with 15 female solder contacts, IP68/69K in unmated conditions, keying Y; UTS714E15SY

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS714E15SY
PRODUCT LENGTH/DEPTH	25.3 mm
PRODUCT HEIGHT	34.9 mm
PRODUCT WIDTH	34.9 mm
PRODUCT WEIGHT	22.2 g
COMPLIANCES	UL 1977 (please contact us for more details) CSA-C22.2 No.182.3 (please contact us for more details) ROHS exemption 6.c IEC 61984 (please contact us for more details)

CURRENT RATING	4 A IEC 12 A UL
ENVIRONMENTAL CONDITIONS	REACH Flammability rating UL94 HB RoHS
ENVIRONMENTAL RESISTANCE	UV resistant, no degradation after 5 years of exposure in natural environment Resistant against gasoline Resistant against mineral oil Resistant against acid bath Resistant against basic bath Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against oil
TEST CURRENT	12 A CSA 12 A UL 4 A IEC
TEST VOLTAGE	600 V CSA 600 V UL 50 V IEC
CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
CONNECTOR ORIENTATION	Y
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold
CONTACT TYPE	Solder Cup
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	15
SHELL MATERIAL	Plastic
SHELL SIZE	14
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C

RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	15
NUMBER OF CAVITY #16	1
NUMBER OF CAVITY #20	14
NUT MATERIAL	Aluminium
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

