

Eaton UTS714E19SY

Plastic jam nut receptacle, without backshell, with 19 female solder contacts, IP68/69K in unmated conditions, keying Y; UTS714E19SY

PRODUCT NAME	Eaton Souriau UTS series plastic waterproof IP68/69k connector
CATALOG NUMBER	UTS714E19SY
PRODUCT LENGTH/DEPTH	25.3 mm
PRODUCT HEIGHT	34.9 mm
PRODUCT WIDTH	34.9 mm
PRODUCT WEIGHT	22.9 g
COMPLIANCES	ROHS exemption 6.c IEC 61984 (please contact us for more details) UL 1977 (please contact us for more details) CSA-C22.2 No.182.3 (please contact us for more details)

CURRENT RATING	5 A IEC 4 A UL
ENVIRONMENTAL CONDITIONS	Flammability rating UL94 HB RoHS REACH
ENVIRONMENTAL RESISTANCE	Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against acid bath
	UV resistant, no degradation after 5 years of exposure in natural environment Resistant against mineral oil Resistant against oil Resistant against basic bath Resistant against gasoline
TEST CURRENT	5 A IEC 4 A CSA 4 A UL
TEST VOLTAGE	32 V IEC 250 V UL 250 V CSA
CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
CONNECTOR ORIENTATION	Y
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Loaded
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold
CONTACT TYPE	Solder Cup
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP68
INSERT MATERIAL	Neoprene
LAYOUT	19
SHELL MATERIAL	Plastic
SHELL SIZE	14
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C



RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	19
NUMBER OF CAVITY #20	19
NUT MATERIAL	Aluminium
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: