



## Eaton UTS78D3APX

Plastic jam nut receptacle, without backshell, with 3 male PCB contacts, IP68/69K in unmated conditions, keying X; UTS78D3APX

□□□□

<b>PRODUCT NAME</b>	Eaton Souriau UTS series plastic waterproof IP68/69k connector
<b>CATALOG NUMBER</b>	UTS78D3APX
<b>PRODUCT LENGTH/DEPTH</b>	25.3 mm
<b>PRODUCT HEIGHT</b>	24 mm
<b>PRODUCT WIDTH</b>	24 mm
<b>PRODUCT WEIGHT</b>	7.2 g
<b>COMPLIANCES</b>	CSA-C22.2 No.182.3 (please contact us for more details) UL 1977 (please contact us for more details) IEC 61984 (please contact us for more details) ROHS exemption 6.c



Powering Business Worldwide

□□□□

□□

<b>CURRENT RATING</b>	7 A UL 7 A IEC
<b>ENVIRONMENTAL CONDITIONS</b>	Flammability rating UL94 HB RoHS REACH
<b>ENVIRONMENTAL RESISTANCE</b>	Resistant against basic bath Vibrations level Per IEC 60512-4 - from 10 to 2000 Hz Resistant against mineral oil Resistant against oil UV resistant, no degradation after 5 years of exposure in natural environment Resistant against gasoline Resistant against acid bath
<b>TEST CURRENT</b>	7 A IEC 7 A CSA 7 A UL
<b>TEST VOLTAGE</b>	250 V UL 50 V IEC 250 V CSA
<b>CONNECTOR ACCESSORY OPTION</b>	No backshell possibility
<b>CONNECTOR ORIENTATION</b>	X
<b>CONNECTOR TYPE</b>	Receptacle
<b>CONTACT DELIVERY</b>	Loaded
<b>CONTACT GENDER</b>	Pin (Male)
<b>CONTACT PLATING</b>	Gold
<b>CONTACT TYPE</b>	PCB
<b>COUPLING TYPE</b>	1/3 Bayonet
<b>DEGREE OF PROTECTION</b>	IP68
<b>INSERT MATERIAL</b>	Neoprene
<b>LAYOUT</b>	D3A
<b>SHELL MATERIAL</b>	Plastic
<b>SHELL SIZE</b>	8
<b>MATING CYCLES</b>	250
<b>OPERATING TEMPERATURE - MAX</b>	105 °C
<b>OPERATING TEMPERATURE - MIN</b>	-40 °C
<b>RECEPTACLE TYPE</b>	Jam Nut Receptacle
<b>NUMBER OF CONTACTS</b>	3

