



□□□□

Eaton UTSX012D14S

Square flange receptacle, without backshell, with 14 female PCB contacts, IP68/69K in unmated conditions; UTSX012D14S

□□□□

PRODUCT NAME	Eaton Souriau UTSX series plastic circular bayonet connector
CATALOG NUMBER	UTSX012D14S
PRODUCT LENGTH/DEPTH	32.3 mm
PRODUCT HEIGHT	26.2 mm
PRODUCT WIDTH	26.2 mm
PRODUCT WEIGHT	14 g

ENVIRONMENTAL CONDITIONS	RoHS
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Delivered with the connector, mounted
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold flash
CONTACT TYPE	PCB
COUPLING TYPE	1/3 Bayonet
LAYOUT	D14
SHELL MATERIAL	Plastic
SHELL SIZE	12
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Square Flange Receptacle
NUMBER OF CONTACTS	14
NUMBER OF CAVITY #20	14
SALT SPRAY	500 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

00: