



□□□□□

Eaton UTSX612E14SW

Plug, without backshell, with 14 female solder contacts, IP68/69K in unmated conditions, keying W; UTSX612E14SW

□□□□

PRODUCT NAME	Eaton Souriau UTSX series plastic circular bayonet connector
CATALOG NUMBER	UTSX612E14SW
PRODUCT LENGTH/DEPTH	24 mm
PRODUCT HEIGHT	29.7 mm
PRODUCT WIDTH	29.7 mm
PRODUCT WEIGHT	22 g

ENVIRONMENTAL CONDITIONS	RoHS
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	W
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Delivered with the connector, mounted
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold flash
CONTACT TYPE	Solder Cup
COUPLING TYPE	1/3 Bayonet
LAYOUT	E14
PLUG TYPE	Straight Plug
SHELL MATERIAL	Plastic
SHELL SIZE	12
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	14
NUMBER OF CAVITY #20	14
SALT SPRAY	500 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

00: