

# Eaton UTSX6JC104PW

Plug, with cable gland backshell, for 4 male contacts, IP68/69K, keying W;  
UTSX6JC104PW

|                      |                                                              |
|----------------------|--------------------------------------------------------------|
|                      |                                                              |
| PRODUCT NAME         | Eaton Souriau UTSX series plastic circular bayonet connector |
| CATALOG NUMBER       | UTSX6JC104PW                                                 |
| PRODUCT LENGTH/DEPTH | 63.2 mm                                                      |
| PRODUCT HEIGHT       | 26.2 mm                                                      |
| PRODUCT WIDTH        | 26.2 mm                                                      |
| PRODUCT WEIGHT       | 20 g                                                         |

|                                    |                          |
|------------------------------------|--------------------------|
| <b>ENVIRONMENTAL CONDITIONS</b>    | RoHS                     |
| <b>BACKSHELL ANGLE</b>             | straight                 |
| <b>BACKSHELL TYPE</b>              | Sealing Gland            |
| <b>CONNECTOR ACCESSORY OPTION</b>  | Delivered with connector |
| <b>CONNECTOR ORIENTATION</b>       | W                        |
| <b>CONNECTOR TYPE</b>              | Plug                     |
| <b>CONTACT DELIVERY</b>            | Not delivered            |
| <b>CONTACT GENDER</b>              | Pin (Male)               |
| <b>CONTACT TYPE</b>                | Crimp                    |
| <b>COUPLING TYPE</b>               | 1/3 Bayonet              |
| <b>LAYOUT</b>                      | 4                        |
| <b>PLUG TYPE</b>                   | Straight Plug            |
| <b>SHELL MATERIAL</b>              | Plastic                  |
| <b>SHELL SIZE</b>                  | 10                       |
| <b>MATING CYCLES</b>               | 250                      |
| <b>OPERATING TEMPERATURE - MAX</b> | 105 °C                   |
| <b>OPERATING TEMPERATURE - MIN</b> | -40 °C                   |
| <b>NUMBER OF CONTACTS</b>          | 4                        |
| <b>NUMBER OF CAVITY #16</b>        | 4                        |
| <b>SALT SPRAY</b>                  | 500 hour                 |

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

