

Eaton UTSX714D7S

Jam nut receptacle, without backshell, with 7 female PCB contacts, IP68/69K in unmated conditions; UTSX714D7S

PRODUCT NAME	Eaton Souriau UTSX series plastic circular bayonet connector
CATALOG NUMBER	UTSX714D7S
PRODUCT LENGTH/DEPTH	24.5 mm
PRODUCT HEIGHT	30.2 mm
PRODUCT WIDTH	30.2 mm
PRODUCT WEIGHT	21 g



FITTED WITH:	Layout with ground cavity
ENVIRONMENTAL CONDITIONS	RoHS
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Delivered with the connector, mounted
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold flash
CONTACT TYPE	PCB
COUPLING TYPE	1/3 Bayonet
LAYOUT	D7
SHELL MATERIAL	Plastic
SHELL SIZE	14
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	7
NUMBER OF CAVITY #16	7
SALT SPRAY	500 hour



PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: