

Eaton UTSX714E15PY

Jam nut receptacle, without backshell, with 15 male solder contacts, IP68/69K in unmated conditions, keying Y; UTSX714E15PY

PRODUCT NAME	Eaton Souriau UTSX series plastic circular bayonet connector
CATALOG NUMBER	UTSX714E15PY
PRODUCT LENGTH/DEPTH	24.5 mm
PRODUCT HEIGHT	30.2 mm
PRODUCT WIDTH	30.2 mm
PRODUCT WEIGHT	18 g

ENVIRONMENTAL CONDITIONS	RoHS
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	Y
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Delivered with the connector, mounted
CONTACT GENDER	Pin (Male)
CONTACT PLATING	Gold flash
CONTACT TYPE	Solder Cup
COUPLING TYPE	1/3 Bayonet
LAYOUT	E15
SHELL MATERIAL	Plastic
SHELL SIZE	14
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	15
SALT SPRAY	500 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

