



□□□□□

Eaton UTSX714E19P

Jam nut receptacle, without backshell, with 19 male solder contacts, IP68/69K in unmated conditions; UTSX714E19P

□□□□

PRODUCT NAME	Eaton Souriau UTSX series plastic circular bayonet connector
CATALOG NUMBER	UTSX714E19P
PRODUCT LENGTH/DEPTH	24.5 mm
PRODUCT HEIGHT	30.2 mm
PRODUCT WIDTH	30.2 mm
PRODUCT WEIGHT	19 g

ENVIRONMENTAL CONDITIONS	RoHS
CONNECTOR ACCESSORY OPTION	No backshell possibility
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Delivered with the connector, mounted
CONTACT GENDER	Pin (Male)
CONTACT PLATING	Gold flash
CONTACT TYPE	Solder Cup
COUPLING TYPE	1/3 Bayonet
LAYOUT	E19
SHELL MATERIAL	Plastic
SHELL SIZE	14
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	19
NUMBER OF CAVITY #20	19
SALT SPRAY	500 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

00: