

Eaton UTSX7JC1492SY

Jam nut receptacle, with cable gland backshell, for 12 female contacts, IP68/69K, keying Y; UTSX7JC1492SY

PRODUCT NAME	Eaton Souriau UTSX series plastic circular bayonet connector
CATALOG NUMBER	UTSX7JC1492SY
PRODUCT LENGTH/DEPTH	84 mm
PRODUCT HEIGHT	30.2 mm
PRODUCT WIDTH	30.2 mm
PRODUCT WEIGHT	35 g

ENVIRONMENTAL CONDITIONS	RoHS
BACKSHELL ANGLE	straight
BACKSHELL TYPE	Sealing Gland
CONNECTOR ACCESSORY OPTION	Delivered with connector
CONNECTOR ORIENTATION	Y
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Socket (Female)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
LAYOUT	92
SHELL MATERIAL	Plastic
SHELL SIZE	14
MATING CYCLES	250
OPERATING TEMPERATURE - MAX	105 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Jam Nut Receptacle
NUMBER OF CONTACTS	12
NUMBER OF CAVITY #16	12
SALT SPRAY	500 hour

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

