

Eaton V2PC22

Eaton Crouse-Hinds series V2PC photocell, 1.8A, 50/60 Hz, Photocell for field installation in lighting fixtures, Used with LMV, DMV, VMV, VMV high wattage, FMV series luminaires, 208-240 Vac

PRODUCT NAME	Eaton Crouse-Hinds series V2PC photocell
CATALOG NUMBER	V2PC22
UPC	782274709369
PRODUCT LENGTH/DEPTH	3.9 in
PRODUCT HEIGHT	3.1 in
PRODUCT WIDTH	4.3 in
PRODUCT WEIGHT	0.35 lb

Certifications and compliances

AREA CLASSIFICATION Hazardous/Classified Locations

STANDARDS TYPE NEC/CEC

NEC HAZARDOUS RATING Class I, Division 2

Product specifications

TYPE Photocell for field installation in lighting fixtures

VOLTAGE RATING 208-240 Vac

FREQUENCY RATING 50/60 Hz

AMPERAGE RATING 1.8A

USED WITH LMV, DMV, VMV, VMV high wattage, FMV series luminaires

[IF 1271 - V2PC Integral Photocell Kit for DMV, VMV, N2MV and FMV Fixtures](#)

[Eaton Specification Sheet - V2PC22](#)

[Crouse-Hinds series Photocells catalog page](#)

[Photocells for Champ HID and Fluorescent Hazardous Area Light Fixtures UL certification](#)

[Photocells for Champ HID and Fluorescent Hazardous Area Light Fixtures Canadian certification](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

