

Eaton V3LM2CA2/UNV1 S896

Eaton Crouse-Hinds series Vaporgard V2L LED, 0.24A, Cool, AC drive, 50W HID or 150-200W incan equiv, Without guard, Heat and impact resistant glass lens, 3000 lm, Copper-free alum, Pend mt, Teflon coated lens, 3/4", 120-277 Vac, 29W

PRODUCT NAME	Eaton Crouse-Hinds series Vaporgard V2L LED light fixture
CATALOG NUMBER	V3LM2CA2/UNV1 S896
UPC	662276652149
PRODUCT LENGTH/DEPTH	8.75 in
PRODUCT HEIGHT	4.69 in
PRODUCT WIDTH	8.75 in
PRODUCT WEIGHT	5.7 lb

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 2
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

LUMENS	3000
COLOR TEMPERATURE	Cool white
MOUNTING METHOD	Pendant
TRADE SIZE	3/4"
VOLTAGE RATING	120-277 Vac
DRIVE TYPE	AC
FREQUENCY RATING	50/60 Hz
LENS MATERIAL	Heat and impact resistant glass
WATTAGE	29W
AMPERAGE RATING	0.24 A
MATERIAL	Copper-free aluminum
POWER FACTOR	> 0.9
GUARD	Without guard
EQUIVALENT LUMINAIRE	50W HID or 150-200W incandescent
SPECIAL FEATURES	Teflon coated lens

[IF 1885 - Vaporgard V2L/V3L Driver Modules - AC Version](#)

[Eaton Specification Sheet - V3LM2CA2/UNV1 S896](#)

[Crouse-Hinds series Global LED lighting portfolio](#)

[Crouse-Hinds series Vaporgard V2L/V3L LED brochure](#)

[Crouse-Hinds series Vaporgard V2L/V3L LED catalog page](#)

[Vaporgard V2L Hazardous Area LED Light Fixtures Canadian certification](#)

[Vaporgard V2L Hazardous Area LED Light Fixtures UL certification](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

