



□□□□

Eaton

V3LM2CHW2/UNV1

Eaton Crouse-Hinds series Vaporgard V2L LED, 0.24A, Cool white, AC drive, 50W HID or 150-200W incan equiv, 50/60 Hz, Without guard, Heat and impact resistant glass lens, 3000 lm, Copper-free alum, VXW wall mt, 3/4", 120-277 Vac, 29W

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series Vaporgard V2L LED light fixture
CATALOG NUMBER	V3LM2CHW2/UNV1
UPC	662276841529
PRODUCT LENGTH/DEPTH	11.25 in
PRODUCT HEIGHT	7.06 in
PRODUCT WIDTH	8.75 in
PRODUCT WEIGHT	7.9 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 2
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

LUMENS	3000
COLOR TEMPERATURE	Cool white
MOUNTING METHOD	VXW wall
TRADE SIZE	3/4"
VOLTAGE RATING	120-277 Vac
DRIVE TYPE	AC
FREQUENCY RATING	50/60 Hz
LENS MATERIAL	Heat and impact resistant glass
WATTAGE	29W
AMPERAGE RATING	0.24 A
MATERIAL	Copper-free aluminum
POWER FACTOR	> 0.9
GUARD	Without guard
EQUIVALENT LUMINAIRE	50W HID or 150-200W incandescent



□□□□□

[IF 1885 - Vaporgard V2L/V3L Driver Modules - AC Version](#)

□□□□□□□

[Eaton Specification Sheet - V3LM2CHW2/UNV1](#)

□□□□

[Crouse-Hinds series Global LED lighting portfolio](#)

□□□□

[Crouse-Hinds series Vaporgard V2L/V3L LED brochure](#)

□□□□

[Crouse-Hinds series Vaporgard V2L/V3L LED catalog page](#)

[Vaporgard V2L Hazardous Area LED Light Fixtures UL certification](#)

[Vaporgard V2L Hazardous Area LED Light Fixtures Canadian certification](#)

