



□□□□□

Eaton V48M28T3016-US

Eaton General purpose ventilated transformer, Fungus pr, AL windings, DOE 2016, NEMA 3R, B, 30 kVA, Made in USA, Fl/wall mt uprt, 3-ph, PV: 480V delta, SV: 208Y/120, NEMA ST-20, 2 at +2.5%, 4 at -2.5%, 30 kVA

□□□□

PRODUCT NAME	Eaton General purpose ventilated transformer
CATALOG NUMBER	V48M28T3016-US
UPC	786680221255
PRODUCT LENGTH/DEPTH	17 in
PRODUCT HEIGHT	32 in
PRODUCT WIDTH	26.5 in
PRODUCT WEIGHT	325 lb
COMPLIANCES	DOE2016 Efficient
CERTIFICATIONS	UL Listed
CATALOG NOTES	10 CFR Part 431 (2016) Efficient



Powering Business Worldwide

SPECIAL FEATURES	Fungus-resistant varnished core and coil, Made in America
TYPE	Energy-efficient ventilated dry-type transformer
COIL MATERIAL	Aluminum
EFFICIENCY	10 CFR Part 431-2016 (DOE 2016)
FREQUENCY RATING	60 Hz
KVA RATING	30 kVA
MOUNTING	Floor or wall, upright only
PHASE	Three-phase
PRIMARY VOLTAGE	480 V delta
SECONDARY VOLTAGE	208Y/120 V
SOUND LEVEL	NEMA ST-20
TEMPERATURE RISE	150 °C rise
VOLTAGE RATING	480 Vac-208Y/120 Vac
ENCLOSURE	NEMA 3R
FRAME	B
INSULATION	220 °C
MATERIAL	Al windings
MODIFICATION 1	Made in America
TAP SIZE	2 at +2.5%, 4 at -2.5%
VOLT AMPERE RATING	30 kVA
WEATHERSHIELD	Not required

□□□□:

□□□□:

□□□:

□□: