

Eaton VGE1B32A13PN

Male square flange receptacle for 13 #12 contacts, insulator orientation N;
VGE1B32A13PN

PRODUCT NAME	Eaton Souriau VGE1-FER1 series fire and smoke certified bayonet connector
CATALOG NUMBER	VGE1B32A13PN
PRODUCT LENGTH/DEPTH	66.8 mm
PRODUCT HEIGHT	66.8 mm
PRODUCT WIDTH	48.1 mm
PRODUCT WEIGHT	122 g

ENVIRONMENTAL CONDITIONS	Fire & Smoke Flammability rating UL94 V0 RoHS REACH
---------------------------------	--

CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
-----------------------------------	---

CONNECTOR ORIENTATION	N
------------------------------	---

CONNECTOR TYPE	Receptacle
-----------------------	------------

CONTACT DELIVERY	Not delivered
-------------------------	---------------

CONTACT GENDER	Pin (Male)
-----------------------	------------

CONTACT TYPE	Crimp
---------------------	-------

COUPLING TYPE	1/3 Bayonet
----------------------	-------------

DEGREE OF PROTECTION	IP67
-----------------------------	------

LAYOUT	A13
---------------	-----

SHELL CONTINUITY	20.0
-------------------------	------

SHELL MATERIAL	Aluminium
-----------------------	-----------

SHELL SIZE	32
-------------------	----

MATING CYCLES	500
----------------------	-----

OPERATING TEMPERATURE - MAX	100 °C
------------------------------------	--------

OPERATING TEMPERATURE - MIN	-40 °C
------------------------------------	--------

RECEPTACLE TYPE	Square Flange Receptacle
------------------------	--------------------------

NUMBER OF CONTACTS	13
---------------------------	----

NUMBER OF CAVITY #12	13
-----------------------------	----

SALT SPRAY	500 hour
-------------------	----------

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:
