

Eaton VGE1B32A13PW

Male square flange receptacle for 13 #12 contacts, insulator orientation W; VGE1B32A13PW

PRODUCT NAME	Eaton Souriau VGE1-FER1 series fire and smoke certified bayonet connector
CATALOG NUMBER	VGE1B32A13PW
PRODUCT LENGTH/DEPTH	66.8 mm
PRODUCT HEIGHT	66.8 mm
PRODUCT WIDTH	48.1 mm
PRODUCT WEIGHT	122 g

ENVIRONMENTAL CONDITIONS	RoHS Fire & Smoke Flammability rating UL94 V0 REACH
CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Receptacle
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP67
LAYOUT	A13
SHELL CONTINUITY	20.0
SHELL MATERIAL	Aluminium
SHELL SIZE	32
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	100 °C
OPERATING TEMPERATURE - MIN	-40 °C
RECEPTACLE TYPE	Square Flange Receptacle
NUMBER OF CONTACTS	13
NUMBER OF CAVITY #12	13
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:

Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

Follow us on social media to get the latest product and support information.