

Eaton VGE1B36A22P0

Male square flange receptacle for 22 #12 contacts, insulator not installed in the shell; VGE1B36A22P0

PRODUCT NAME	Eaton Souriau VGE1-FER1 series fire and smoke certified bayonet connector
CATALOG NUMBER	VGE1B36A22P0
PRODUCT LENGTH/DEPTH	50.8 mm
PRODUCT HEIGHT	50.8 mm
PRODUCT WIDTH	48 mm
PRODUCT WEIGHT	149 g

ENVIRONMENTAL CONDITIONS	RoHS REACH Flammability rating UL94 V0 Fire & Smoke
--------------------------	--

CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
----------------------------	---

CONNECTOR ORIENTATION	W
-----------------------	---

CONNECTOR TYPE	Receptacle
----------------	------------

CONTACT DELIVERY	Not delivered
------------------	---------------

CONTACT GENDER	Pin (Male)
----------------	------------

CONTACT TYPE	Crimp
--------------	-------

COUPLING TYPE	1/3 Bayonet
---------------	-------------

DEGREE OF PROTECTION	IP67
----------------------	------

LAYOUT	A22
--------	-----

SHELL CONTINUITY	20.0
------------------	------

SHELL MATERIAL	Aluminium
----------------	-----------

SHELL SIZE	36
------------	----

MATING CYCLES	500
---------------	-----

OPERATING TEMPERATURE - MAX	100 °C
-----------------------------	--------

OPERATING TEMPERATURE - MIN	-40 °C
-----------------------------	--------

RECEPTACLE TYPE	Square Flange Receptacle
-----------------	--------------------------

NUMBER OF CONTACTS	22
--------------------	----

NUMBER OF CAVITY #12	22
----------------------	----

SALT SPRAY	500 hour
------------	----------

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

