

Eaton VGE1D2015SX

Female plug for 7 #12 contacts, insulator orientation X; VGE1D2015SX

PRODUCT NAME	Eaton Souriau VGE1-FER1 series fire and smoke certified bayonet connector
CATALOG NUMBER	VGE1D2015SX
PRODUCT LENGTH/DEPTH	35 mm
PRODUCT HEIGHT	35 mm
PRODUCT WIDTH	44.8 mm
PRODUCT WEIGHT	62 g

ENVIRONMENTAL CONDITIONS	REACH RoHS Fire & Smoke Flammability rating UL94 V0
--------------------------	--

CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
----------------------------	---

CONNECTOR ORIENTATION	N
-----------------------	---

CONNECTOR TYPE	Plug
----------------	------

CONTACT DELIVERY	Not delivered
------------------	---------------

CONTACT GENDER	Socket (Female)
----------------	-----------------

CONTACT PLATING	Gold
-----------------	------

CONTACT TYPE	Crimp
--------------	-------

COUPLING TYPE	1/3 Bayonet
---------------	-------------

DEGREE OF PROTECTION	IP67
----------------------	------

LAYOUT	15
--------	----

PLUG TYPE	Straight Plug
-----------	---------------

SHELL CONTINUITY	20.0
------------------	------

SHELL MATERIAL	Aluminium
----------------	-----------

SHELL SIZE	20
------------	----

MATING CYCLES	500
---------------	-----

OPERATING TEMPERATURE - MAX	100 °C
-----------------------------	--------

OPERATING TEMPERATURE - MIN	-40 °C
-----------------------------	--------

NUMBER OF CONTACTS	7
--------------------	---

NUMBER OF CAVITY #12	7
----------------------	---

SALT SPRAY	500 hour
------------	----------

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:
