

Eaton VGE1D2015SZ

Female plug for 7 #12 contacts, insulator orientation Z; VGE1D2015SZ

PRODUCT NAME	Eaton Souriau VGE1-FER1 series fire and smoke certified bayonet connector
CATALOG NUMBER	VGE1D2015SZ
PRODUCT LENGTH/DEPTH	41 mm
PRODUCT HEIGHT	41 mm
PRODUCT WIDTH	44.8 mm
PRODUCT WEIGHT	62 g

ENVIRONMENTAL CONDITIONS	RoHS Fire & Smoke Flammability rating UL94 V0 REACH
---------------------------------	--

CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
-----------------------------------	---

CONNECTOR ORIENTATION	Y
------------------------------	---

CONNECTOR TYPE	Plug
-----------------------	------

CONTACT DELIVERY	Not delivered
-------------------------	---------------

CONTACT GENDER	Socket (Female)
-----------------------	-----------------

CONTACT PLATING	Gold
------------------------	------

CONTACT TYPE	Crimp
---------------------	-------

COUPLING TYPE	1/3 Bayonet
----------------------	-------------

DEGREE OF PROTECTION	IP67
-----------------------------	------

LAYOUT	15
---------------	----

PLUG TYPE	Straight Plug
------------------	---------------

SHELL CONTINUITY	20.0
-------------------------	------

SHELL MATERIAL	Aluminium
-----------------------	-----------

SHELL SIZE	20
-------------------	----

MATING CYCLES	500
----------------------	-----

OPERATING TEMPERATURE - MAX	100 °C
------------------------------------	--------

OPERATING TEMPERATURE - MIN	-40 °C
------------------------------------	--------

NUMBER OF CONTACTS	7
---------------------------	---

NUMBER OF CAVITY #12	7
-----------------------------	---

SALT SPRAY	500 hour
-------------------	----------

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:
