

Eaton VGE1D2410SZ

Female plug for 7 #8 contacts, insulator orientation Z; VGE1D2410SZ

PRODUCT NAME	Eaton Souriau VGE1-FER1 series fire and smoke certified bayonet connector
CATALOG NUMBER	VGE1D2410SZ
PRODUCT LENGTH/DEPTH	50.8 mm
PRODUCT HEIGHT	50.8 mm
PRODUCT WIDTH	41.2 mm
PRODUCT WEIGHT	80 g



ENVIRONMENTAL CONDITIONS	Flammability rating UL94 V0 Fire & Smoke RoHS REACH
CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
CONNECTOR ORIENTATION	N
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Socket (Female)
CONTACT PLATING	Gold
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP67
LAYOUT	10
PLUG TYPE	Straight Plug
SHELL CONTINUITY	20.0
SHELL MATERIAL	Aluminium
SHELL SIZE	24
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	100 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	7
NUMBER OF CAVITY #8 POWER	7
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

