

Eaton VGE1D36A22SZ

Female plug for 22 #12 contacts, insulator orientation Z; VGE1D36A22SZ

PRODUCT NAME	Eaton Souriau VGE1-FER1 series fire and smoke certified bayonet connector
CATALOG NUMBER	VGE1D36A22SZ
PRODUCT LENGTH/DEPTH	44 mm
PRODUCT HEIGHT	44 mm
PRODUCT WIDTH	45.6 mm
PRODUCT WEIGHT	169 g

ENVIRONMENTAL CONDITIONS	REACH RoHS Flammability rating UL94 V0 Fire & Smoke
--------------------------	--

CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
----------------------------	---

CONNECTOR ORIENTATION	Insulator not mounted
-----------------------	-----------------------

CONNECTOR TYPE	Plug
----------------	------

CONTACT DELIVERY	Not delivered
------------------	---------------

CONTACT GENDER	Socket (Female)
----------------	-----------------

CONTACT TYPE	Crimp
--------------	-------

COUPLING TYPE	1/3 Bayonet
---------------	-------------

DEGREE OF PROTECTION	IP67
----------------------	------

LAYOUT	A22
--------	-----

PLUG TYPE	Straight Plug
-----------	---------------

SHELL CONTINUITY	20.0
------------------	------

SHELL MATERIAL	Aluminium
----------------	-----------

SHELL SIZE	36
------------	----

MATING CYCLES	500
---------------	-----

OPERATING TEMPERATURE - MAX	100 °C
-----------------------------	--------

OPERATING TEMPERATURE - MIN	-40 °C
-----------------------------	--------

NUMBER OF CONTACTS	22
--------------------	----

NUMBER OF CAVITY #12	22
----------------------	----

SALT SPRAY	500 hour
------------	----------

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:
