

Eaton VGE1D40A35PN

Male plug for 35 #12 contacts, insulator orientation N; VGE1D40A35PN

PRODUCT NAME	Eaton Souriau VGE1-FER1 series fire and smoke certified bayonet connector
CATALOG NUMBER	VGE1D40A35PN
PRODUCT LENGTH/DEPTH	44 mm
PRODUCT HEIGHT	44 mm
PRODUCT WIDTH	45.6 mm
PRODUCT WEIGHT	163 g



ENVIRONMENTAL CONDITIONS	Fire & Smoke
	RoHS
	Flammability rating UL94
	V0
	REACH
CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
CONNECTOR ORIENTATION	Insulator not mounted
CONNECTOR TYPE	Plug
CONTACT DELIVERY	Not delivered
CONTACT GENDER	Pin (Male)
CONTACT TYPE	Crimp
COUPLING TYPE	1/3 Bayonet
DEGREE OF PROTECTION	IP67
LAYOUT	A35
PLUG TYPE	Straight Plug
SHELL CONTINUITY	20.0
SHELL MATERIAL	Aluminium
SHELL SIZE	40
MATING CYCLES	500
OPERATING TEMPERATURE - MAX	100 °C
OPERATING TEMPERATURE - MIN	-40 °C
NUMBER OF CONTACTS	35
NUMBER OF CAVITY #12	35
SALT SPRAY	500 hour

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:

