

Eaton VGE1D40A35SN

Female plug for 35 #12 contacts, insulator orientation N; VGE1D40A35SN

PRODUCT NAME	Eaton Souriau VGE1-FER1 series fire and smoke certified bayonet connector
CATALOG NUMBER	VGE1D40A35SN
PRODUCT LENGTH/DEPTH	44 mm
PRODUCT HEIGHT	44 mm
PRODUCT WIDTH	45.6 mm
PRODUCT WEIGHT	201 g

ENVIRONMENTAL CONDITIONS	Flammability rating UL94 V0 REACH Fire & Smoke RoHS
--------------------------	--

CONNECTOR ACCESSORY OPTION	Not delivered, to be ordered separately
----------------------------	---

CONNECTOR ORIENTATION	X
-----------------------	---

CONNECTOR TYPE	Plug
----------------	------

CONTACT DELIVERY	Not delivered
------------------	---------------

CONTACT GENDER	Socket (Female)
----------------	-----------------

CONTACT TYPE	Crimp
--------------	-------

COUPLING TYPE	1/3 Bayonet
---------------	-------------

DEGREE OF PROTECTION	IP67
----------------------	------

LAYOUT	A35
--------	-----

PLUG TYPE	Straight Plug
-----------	---------------

SHELL CONTINUITY	20.0
------------------	------

SHELL MATERIAL	Aluminium
----------------	-----------

SHELL SIZE	40
------------	----

MATING CYCLES	500
---------------	-----

OPERATING TEMPERATURE - MAX	100 °C
-----------------------------	--------

OPERATING TEMPERATURE - MIN	-40 °C
-----------------------------	--------

NUMBER OF CONTACTS	35
--------------------	----

NUMBER OF CAVITY #12	35
----------------------	----

SALT SPRAY	500 hour
------------	----------

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:
