



□□□□

Eaton VMVL-11-2A-R3-G-UNV1-S891

Eaton Crouse-Hinds series Champ VMVL LED fixture, Cool white, 320W HID equivalent, Wire guard, Diffused glass lens, 11000 lumens, 122 lm/W, Die cast aluminum, Pendant mount, Type III, 3/4" trade size, 100-277 Vac, 127-250 Vdc, 92W

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series Champ VMVL LED light fixture
CATALOG NUMBER	VMVL-11-2A-R3-G-UNV1-S891
UPC	662276914124
PRODUCT LENGTH/DEPTH	11.62 in
PRODUCT HEIGHT	11 in
PRODUCT WIDTH	11.62 in
PRODUCT WEIGHT	20.45 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC IEC IECEX/ATEX
NEC HAZARDOUS RATING	Class I, Division 2 Class I, Zone 2 Class II, Division 1 Class III
IECEX/ATEX HAZARDOUS RATING	Zone 21
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66



3D

[SP3D Design Package - Champ VMVL LED Hazardous Area Light Fixtures](#)

[IF 1888 - Champ VMVL and PVML Driver Replacement](#)
[IF 1882 - Champ VMVL and PVML LED luminaires](#)

[Champ VMV LED Hazardous Area](#)

[Eaton Specification Sheet - VMVL-11-2A-R3-G-UNV1-S891](#)

[Crouse-Hinds series DLC approved lighting products](#)

[Crouse-Hinds series Champ VMVL LED Luminaires - 3,000 to 13,000 lumens brochure](#)

[Crouse-Hinds series Global LED lighting portfolio](#)

[Crouse-Hinds series Champ VMVL LED luminaires - 3,000 to 13,000 lumens catalog page](#)

Product specifications

LUMENS	11000
LUMENS PER WATT	75
COLOR TEMPERATURE	Cool white
MOUNTING METHOD	Pendant
TRADE SIZE	100-240 Vac, 127-250 Vdc
OPTICAL DISTRIBUTION	Type III
GUARD TYPE	Wire
VOLTAGE RATING	100-277 Vac, 127-250 Vdc
FREQUENCY RATING	50/60 Hz
WATTAGE	92W
POWER FACTOR	> 0.90
EQUIVALENT LUMINAIRE	320W HID
MATERIAL	Die cast aluminum
LENS MATERIAL	Diffused Glass

