

Eaton VMVL-11-2TW-R3-G-UNV1-S890

Eaton Crouse-Hinds series Champ VMVL LED fixture, Cool white, 320W HID equivalent, Wire guard, Glass lens, 11000 lumens, 122 lm/W, Die cast aluminum, Wall mount, Type III, Quick-Clip, 3/4" trade size, 100-277 Vac, 127-250 Vdc, 92W

PRODUCT NAME	Eaton Crouse-Hinds series Champ VMVL LED light fixture
CATALOG NUMBER	VMVL-11-2TW-R3-G-UNV1-S890
UPC	662276968998
PRODUCT LENGTH/DEPTH	13.96 in
PRODUCT HEIGHT	11.31 in
PRODUCT WIDTH	11.62 in
PRODUCT WEIGHT	23.7 lb

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC IEC IECEX/ATEX
NEC HAZARDOUS RATING	Class I, Division 2 Class I, Zone 2 Class II, Division 1 Class III
IECEX/ATEX HAZARDOUS RATING	Zone 21
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

LUMENS	11000
LUMENS PER WATT	75
COLOR TEMPERATURE	Cool white
MOUNTING METHOD	Wall
TRADE SIZE	100-240 Vac, 127-250 Vdc
OPTICAL DISTRIBUTION	Type III
GUARD TYPE	Wire
VOLTAGE RATING	100-277 Vac, 127-250 Vdc
FREQUENCY RATING	50/60 Hz
WATTAGE	92W
POWER FACTOR	> 0.90
EQUIVALENT LUMINAIRE	320W HID
MATERIAL	Die cast aluminum
LENS MATERIAL	Heat and impact resistant glass
SPECIAL FEATURES	Quick-Clip



3D	SP3D Design Package - Champ VMVL LED Hazardous Area Light Fixtures
	IF 1888 - Champ VMVL and PVML Driver Replacement IF 1882 - Champ VMVL and PVML LED luminaires
	Eaton Specification Sheet - VMVL-11-2TW-R3-G-UNV1- S890 Champ VMV LED Hazardous Area
	Crouse-Hinds series DLC approved lighting products Crouse-Hinds series Global LED lighting portfolio Crouse-Hinds series Champ VMVL LED Luminaires - 3,000 to 13,000 lumens brochure
	Crouse-Hinds series Champ VMVL LED luminaires - 3,000 to 13,000 lumens catalog page

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

