

Eaton VMVL-11-J-UNV1

Eaton Crouse-Hinds series Champ VMVL LED fixture, Cool white, 320W HID equivalent, No guard, Glass lens, 11000 lumens, 122 lm/W, Die cast aluminum, Stanchion 25° angled, Type V, 1-1/2" trade size, 100-277 Vac, 127-250 Vdc, 92W

PRODUCT NAME	Eaton Crouse-Hinds series Champ VMVL LED light fixture
CATALOG NUMBER	VMVL-11-J-UNV1
UPC	662276894327
PRODUCT LENGTH/DEPTH	15.07 in
PRODUCT HEIGHT	12.85 in
PRODUCT WIDTH	11.62 in
PRODUCT WEIGHT	22.7 lb

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC IEC IECEX/ATEX
NEC HAZARDOUS RATING	Class I, Division 2 Class I, Zone 2 Class II, Division 1 Class III
IECEX/ATEX HAZARDOUS RATING	Zone 21
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

LUMENS	11000
LUMENS PER WATT	75
COLOR TEMPERATURE	Cool white
MOUNTING METHOD	Stanchion 25° angled
TRADE SIZE	1-1/2"
OPTICAL DISTRIBUTION	Type V
GUARD TYPE	No guard
VOLTAGE RATING	100-277 Vac, 127-250 Vdc
FREQUENCY RATING	50/60 Hz
WATTAGE	92W
POWER FACTOR	> 0.90
EQUIVALENT LUMINAIRE	320W HID
MATERIAL	Die cast aluminum
LENS MATERIAL	Heat and impact resistant glass



3D	SP3D Design Package - Champ VMVL LED Hazardous Area Light Fixtures
	IF 1882 - Champ VMVL and PVML LED luminaires
	IF 1888 - Champ VMVL and PVML Driver Replacement
	Eaton Specification Sheet - VMVL-11-J-UNV1
	Champ VMV LED Hazardous Area
	Crouse-Hinds series Champ VMVL LED Luminaires - 3,000 to 13,000 lumens brochure
	Crouse-Hinds series DLC approved lighting products
	Crouse-Hinds series Global LED lighting portfolio
	Crouse-Hinds series Champ VMVL LED luminaires - 3,000 to 13,000 lumens catalog page

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

