



□□□□□

Eaton VMVL-3-3C-UNV1

Eaton Crouse-Hinds series Champ VMVL LED fixture, Cool white, 70W HID equivalent, No guard, Glass lens, 3000 lumens, 122 lm/W, Die cast aluminum, Ceiling mount, Type V, 1" trade size, 100-277 Vac, 127-250 Vdc, 27W

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series Champ VMVL LED light fixture
CATALOG NUMBER	VMVL-3-3C-UNV1
UPC	662276879928
PRODUCT LENGTH/DEPTH	11.83 in
PRODUCT HEIGHT	11.03 in
PRODUCT WIDTH	10.77 in
PRODUCT WEIGHT	21.75 lb






Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC IEC IECEX/ATEX
NEC HAZARDOUS RATING	Class I, Division 2 Class I, Zone 2 Class II, Division 1 Class III
IECEX/ATEX HAZARDOUS RATING	Zone 21
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

LUMENS	3000
LUMENS PER WATT	122
COLOR TEMPERATURE	Cool white
MOUNTING METHOD	Ceiling
TRADE SIZE	1"
OPTICAL DISTRIBUTION	Type V
GUARD TYPE	No guard
VOLTAGE RATING	100-277 Vac, 127-250 Vdc
FREQUENCY RATING	50/60 Hz
WATTAGE	27W
POWER FACTOR	> 0.90
EQUIVALENT LUMINAIRE	70W HID
MATERIAL	Die cast aluminum
LENS MATERIAL	Heat and impact resistant glass

Resources

3D 	SP3D Design Package - Champ VMVL LED Hazardous Area Light Fixtures
	IF 1882 - Champ VMVL and PVML LED luminaires IF 1888 - Champ VMVL and PVML Driver Replacement
	Eaton Specification Sheet - VMVL-3-3C-UNV1 Champ VMV LED Hazardous Area
	Crouse-Hinds series Champ VMVL LED Luminaires - 3,000 to 13,000 lumens brochure Crouse-Hinds series Global LED lighting portfolio Crouse-Hinds series DLC approved lighting products
	Crouse-Hinds series Champ VMVL LED luminaires - 3,000 to 13,000 lumens catalog page

