



□□□□

Eaton VMVL-7-N-R3-UNV34

Eaton Crouse-Hinds series Champ VMVL LED fixture, Neutral white, 175W HID equivalent, No guard, Glass lens, 7000 lumens, 130 lm/W, Die cast aluminum, No mounting module, Type III, 347-480 Vac, 57W

□□□□

PRODUCT NAME	Eaton Crouse-Hinds series Champ VMVL LED light fixture
CATALOG NUMBER	VMVL-7-N-R3-UNV34
UPC	662276943742
PRODUCT LENGTH/DEPTH	13 in
PRODUCT HEIGHT	13.13 in
PRODUCT WIDTH	12.75 in
PRODUCT WEIGHT	20.8 lb



Powering Business Worldwide

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC IEC IECEX/ATEX
NEC HAZARDOUS RATING	Class I, Division 2 Class I, Zone 2 Class II, Division 1 Class III
IECEX/ATEX HAZARDOUS RATING	Zone 21
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66



3D

[SP3D Design Package - Champ VMVL LED Hazardous Area Light Fixtures](#)

[IF 1888 - Champ VMVL and PVML Driver Replacement](#)
[IF 1882 - Champ VMVL and PVML LED luminaires](#)

[Champ VMV LED Hazardous Area](#)
[Eaton Specification Sheet - VMVL-7-N-R3-UNV34](#)

[Crouse-Hinds series DLC approved lighting products](#)
[Crouse-Hinds series Champ VMVL LED Luminaires - 3,000 to 13,000 lumens brochure](#)
[Crouse-Hinds series Global LED lighting portfolio](#)

[Crouse-Hinds series Champ VMVL LED luminaires - 3,000 to 13,000 lumens catalog page](#)

Product specifications

LUMENS	7000
LUMENS PER WATT	130
COLOR TEMPERATURE	Neutral white
MOUNTING METHOD	No mounting module
OPTICAL DISTRIBUTION	Type III
GUARD TYPE	No guard
VOLTAGE RATING	347-480 Vac
FREQUENCY RATING	50/60 Hz
WATTAGE	57W
POWER FACTOR	> 0.90
EQUIVALENT LUMINAIRE	175W HID
MATERIAL	Die cast aluminum
LENS MATERIAL	Heat and impact resistant glass

