

Eaton VMVL-9-N-UNV1

Eaton Crouse-Hinds series Champ VMVL LED fixture, Neutral white, 250W HID equivalent, No guard, Glass lens, 9000 lumens, 123 lm/W, Die cast aluminum, No mounting module, Type V, 100-277 Vac, 127-250 Vdc, 75W

PRODUCT NAME	Eaton Crouse-Hinds series Champ VMVL LED light fixture
CATALOG NUMBER	VMVL-9-N-UNV1
UPC	662276897977
PRODUCT LENGTH/DEPTH	13 in
PRODUCT HEIGHT	13.13 in
PRODUCT WIDTH	12.75 in
PRODUCT WEIGHT	20.8 lb

Certifications and compliances

AREA CLASSIFICATION	Hazardous/Classified Locations
STANDARDS TYPE	NEC/CEC IEC IECEX/ATEX
NEC HAZARDOUS RATING	Class I, Division 2 Class I, Zone 2 Class II, Division 1 Class III
IECEX/ATEX HAZARDOUS RATING	Zone 21
NEMA RATING	4X
INGRESS PROTECTION (IP) RATINGS	IP66

Product specifications

LUMENS	9000
LUMENS PER WATT	123
COLOR TEMPERATURE	Neutral white
MOUNTING METHOD	No mounting module
OPTICAL DISTRIBUTION	Type V
GUARD TYPE	No guard
VOLTAGE RATING	100-277 Vac, 127-250 Vdc
FREQUENCY RATING	50/60 Hz
WATTAGE	75W
POWER FACTOR	> 0.90
EQUIVALENT LUMINAIRE	250W HID
MATERIAL	Die cast aluminum
LENS MATERIAL	Heat and impact resistant glass

3D

[SP3D Design Package -
Champ VMVL LED
Hazardous Area Light
Fixtures](#)

[IF 1888 - Champ VMVL and
PVML Driver Replacement](#)

[IF 1882 - Champ VMVL and
PVML LED luminaires](#)

[Eaton Specification Sheet -
VMVL-9-N-UNV1](#)

[Champ VMV LED
Hazardous Area](#)

[Crouse-Hinds series
Global LED lighting
portfolio](#)

[Crouse-Hinds series
Champ VMVL LED
Luminaires - 3,000 to
13,000 lumens brochure](#)

[Crouse-Hinds series DLC
approved lighting
products](#)

[Crouse-Hinds series
Champ VMVL LED
luminaires - 3,000 to
13,000 lumens catalog
page](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

