



□□□□

## Eaton XJ128 HDG

Eaton Crouse-Hinds series XJG expansion coupling, Rigid/IMC, Steel, Hot dip galvanized finish, 8" maximum conduit movement, 5" trade size

□□□□

<b>PRODUCT NAME</b>	Eaton Crouse-Hinds series XJG expansion coupling
<b>CATALOG NUMBER</b>	XJ128 HDG
<b>UPC</b>	662276271173
<b>PRODUCT LENGTH/DEPTH</b>	14.75 in
<b>PRODUCT HEIGHT</b>	7.64 in
<b>PRODUCT WIDTH</b>	7.64 in
<b>PRODUCT WEIGHT</b>	46 lb



Powering Business Worldwide

## Certifications and compliances

<b>AREA CLASSIFICATION</b>	Ordinary/Non-Hazardous Locations
<b>STANDARDS TYPE</b>	NEC/CEC

### □□

□□□□ [IF 1469 - 5 and 6 Type XI Expansion Joints](#)

□□□□□□ [Eaton Specification Sheet - X128 HDG Expansion and Deflection Couplings](#)

□□□□ [Crouse-Hinds series Conduit Expansion/Deflection Couplings brochure](#)

[Crouse-Hinds series Hot Dip Galvanized Products brochure](#)

□□□□ [Crouse-Hinds series XIG Conduit Expansion Couplings for Rigid/IMC catalog page](#)

□□□□ [XIG Conduit Expansion Couplings for EMT and Rigid/IMC Canadian certification](#)

[XIG Conduit Expansion Couplings for EMT and Rigid/IMC UL certification](#)

## Product specifications

<b>TYPE</b>	Expansion
<b>CONDUIT TYPE</b>	Rigid/IMC
<b>TRADE SIZE</b>	5"
<b>CONDUIT MOVEMENT - MAX</b>	8"
<b>MATERIAL</b>	Steel
<b>FINISH</b>	Hot dip galvanized

