

Eaton XTT3C112

Eaton Crouse-Hinds series XTT dry-type transformer, 60 Hz, 112.5 kVA, Painted steel, Three-phase, 480 Vac primary voltage, 240 Vac secondary voltage, Copper windings, Resin encapsulated

PRODUCT NAME	Eaton Crouse-Hinds series XTT dry-type transformer
CATALOG NUMBER	XTT3C112
UPC	662276963207
PRODUCT LENGTH/DEPTH	36.36 in
PRODUCT HEIGHT	25.63 in
PRODUCT WIDTH	30.75 in
PRODUCT WEIGHT	2253 lb

SPECIAL FEATURES	Copper windings
TYPE	Resin encapsulated
AREA CLASSIFICATION	Hazardous/Classified Locations
FREQUENCY RATING	60 Hz
KVA	112.5 kVA
PHASE	Three-phase
PRIMARY VOLTAGE	480 Vac
SECONDARY VOLTAGE	240 Vac
STANDARDS TYPE	NEC/CEC
NEC HAZARDOUS RATING	Class I, Division 2
NEMA RATING	4
MATERIAL	Painted steel

3D	SP3D Design Package - XDT and XTT Hazardous Area Transformers
	IF XDT - XDT Series Hazardous Area Transformers
	Eaton Specification Sheet - XTT3C112
	XDT Hazardous Area Transformers
	XDT and XTT Hazardous Area Transformers Flyer
	XDT and XTT Hazardous Area Transformers catalog page
	XDT and XTT Hazardous Area Transformers UL certification
	XDT and XTT Hazardous Area Transformers Canadian certification

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
 30 Pembroke Road
 Dublin 4,
 Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

