

Eaton Z20N11E10CU

10 kVA Class 1 Division 2 Transformer, 1PH,
240X480-120/240, shielded, Copper
Windings, NEMA 3R Enclosure

PRODUCT NAME	Eaton Hazardous location encapsulated transformer
CATALOG NUMBER	Z20N11E10CU
UPC	786680233722
PRODUCT LENGTH/DEPTH	1.1 in
PRODUCT HEIGHT	1.1 in
PRODUCT WIDTH	1.1 in
PRODUCT WEIGHT	1.1 lb
COMPLIANCES	Class I, Div. 2, Groups A, B, C, D
CERTIFICATIONS	UL Listed ABS Certified

SPECIAL FEATURES	Shielded
TYPE	Class 1 Division 2 Groups A, B, C and D, Hazardous Location Transformer
AREA CLASSIFICATION	Hazardous/Classified Locations
COIL MATERIAL	Copper
FREQUENCY RATING	50/60 Hz
KVA RATING	10 kVA
KVA	10 kVA
PHASE	Single-phase
PRIMARY VOLTAGE	240 V, 480 V
SECONDARY VOLTAGE	120/240 V
SOUND LEVEL	NEMA ST-20
TEMPERATURE RISE	115 °C rise
ENCLOSURE	NEMA 3R
INSULATION	180 °C
TAP SIZE	None
VOLT AMPERE RATING	10 kVA
WEATHERSHIELD	Indoor-Outdoor

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

