



Eaton B122-000-60

HDMI Signal Booster / Extender, 1920 x 1200 (1080p) 60Hz, Up to 125 ft. (38 m), (HDMI F/F), TAA

□□□□

PRODUCT NAME	Eaton Tripp Lite series signal booster
CATALOG NUMBER	B122-000-60
UPC	037332160294
PRODUCT LENGTH/DEPTH	1.02 in
PRODUCT HEIGHT	2.36 in
PRODUCT WIDTH	0.6 in
PRODUCT WEIGHT	0.1 lb
WARRANTY	3 year limited
COMPLIANCES	RoHS CE Marked FCC Compliant REACH

□□□□	
TYPE	Signal Booster
AUDIO SPECIFICATION	Pass-through audio
AUDIO PORTS	HDMI (FEMALE) HDMI (Female) port allows for pass-through audio
RELATIVE HUMIDITY	0-85% non-condensing
AUDIO INPUT	HDMI
COLOR	Black
AUDIO OUTPUT	HDMI
INPUT	Unit (optional)
MATERIAL	Plastic
CONNECTOR TYPE	Video
PRODUCT FEATURES	TAA Compliant Consumer Electronics Control (CEC) Supported 3D Video Supported EDID Compatible
COLOR DEPTH	24-bit True color 24-bit True Color
PACKAGE CONTENTS	Owner's manual B122-000-60 HDMI Signal Booster
PRODUCT HIGHLIGHTS	3-year limited warranty (Worldwide) Delivers HD picture quality at resolutions up to 1920 x 1200 (1080p) @ 60 Hz Plug-and-play operation with no software required for easy, immediate installation Supports DTS-HD, Dolby TrueHD and 7.1 surround sound for rich, clear audio Allows you to store expensive source device in a secure location for controlled access Compact unit fits easily into briefcase or laptop bag for instant use anywhere
PACKAGING TYPE	Box
CHROMA SUB SAMPLING	4:4:4
POWER SOURCE TYPE	USB
HDCP SPECIFICATION	1.4
SIDEA CONNECTOR1	HDMI (FEMALE)
SIDEB CONNECTOR1	HDMI (FEMALE) MICRO-USB B (FEMALE)

□□

SIDEA CONNECTOR2	MICRO-USB B (FEMALE)
SIDEB CONNECTOR3	HDMI (FEMALE)
POWER SOURCE	Unit (optional)
TECHNOLOGY	HDMI
FEATURES	Flex Center
VIDEO PORTS DETAILS	• HDMI 2.0 • HDCP 2.2
CONNECTOR GROUP	HDMI
CONNECTOR	HDMI (female)
NUMBER OF DISPLAYS	1
NUMBER OF MONITORS SUPPORTED	1
HOUSING	Plastic
MAX SUPPORTED VIDEO RESOLUTION	1920 x 1080 (1080p @ 60Hz)
OPERATING TEMPERATURE RANGE	32° to 104°F (0° to 40°C)
RESOLUTIONS SUPPORTED	1080p @ 60 Hz, up to 125-ft.
STORAGE TEMPERATURE RANGE	5° to 122°F (-15° to 50°C)
VIDEO INPUT	HDMI (FEMALE)
VIDEO OUTPUT	HDMI (FEMALE)
MAX 1024 X 768 RANGE (FT)	150 ft
MAX 1080I RANGE (FT)	150 ft
MAX 1080P RANGE (FT)	150 ft
MAX 1440 X 900 RANGE (FT)	150 ft
MAX 1600 X 1200 RANGE (FT)	150 ft
MAX 480I RANGE (FT)	154 ft
MAX 480P RANGE (FT)	154 ft
MAX 640 X 480 RANGE (FT)	150 ft
MAX 720P RANGE (FT)	150 ft
MAX 800 X 600 RANGE (FT)	150 ft
VIDEO PORTS	HDMI (FEMALE)
NUMBER OF PORTS	1
MAX RESOLUTION	1080p
EXTENDER STYLE	Box
EXTENSION METHOD	HDMI Cable
TAA COMPLIANCE	Yes

Box

□□:

