



Eaton B156-003-HD-V2

3-Port DisplayPort to HDMI Multi-Monitor
Splitter, MST Hub, 4K 60 Hz UHD, DP1.2, TAA

□□□□

PRODUCT NAME	Eaton Tripp Lite series splitter
CATALOG NUMBER	B156-003-HD-V2
UPC	037332193346
PRODUCT LENGTH/DEPTH	6.4 in
PRODUCT HEIGHT	8.1 in
PRODUCT WIDTH	2.17 in
PRODUCT WEIGHT	0.15 lb
WARRANTY	3 year limited
COMPLIANCES	REACH FCC Compliant RoHS

□□□□	
TYPE	Splitter
AUDIO SPECIFICATION	7.1 Channel Surround Sound, DTS-HD and Dolby TrueHD
AC POWER ADAPTER PLUG(S)	NEMA 1-15P North America
RELATIVE HUMIDITY	0-85% non-condensing
COLOR	Black
MATERIAL	Plastic
CONNECTOR PLATING	Nickel
CONNECTOR TYPE	Video
PRODUCT FEATURES	TAA Compliant EDID Compatible 3D Video Supported MST Support
COLOR DEPTH	48-bit Deep color
PACKAGE CONTENTS	External power supply w/NEMA 1-15P plug and 5 ft. cord (Input: 100-240V, 50/60 Hz, 0.5A; Output: 5V, 2A) Owner's manual B156-003-HD-V2 3-Port DisplayPort 1.2 to HDMI MST Hub
PRODUCT HIGHLIGHTS	3-year limited warranty (Worldwide) Built-in 6 in. cable connects directly to DisplayPort source Supports DTS-HD, Dolby TrueHD and 7.1-channel surround sound Works with all operating systems Supports UHD video resolutions up to 4K @ 60Hz (3840 x 2160) Supports up to 48-bit Deep Color (16 bits per channel)
CONTACT PLATING	Gold
PACKAGING TYPE	Box
POWER SOURCE TYPE	AC Adapter
HDCP SPECIFICATION	1.3
SIDEA CONNECTOR1	DISPLAYPORT (MALE)
SIDEB CONNECTOR1	HDMI (FEMALE)
DC BARREL PLUG	OD: 5.5 x 2.1 x 9.5 mm, positive pin, negative sleeve

□□

SIDE B CONNECTOR3	HDMI (FEMALE)
DISPLAYPORT SPECIFICATION	1.2
HOST CONNECTOR	DISPLAYPORT (MALE)
TECHNOLOGY	HDMI DisplayPort
FEATURES	Flex Center
CONNECTOR GROUP	HDMI DisplayPort
CONNECTOR	HDMI (female) DisplayPort (male)
AC POWER ADAPTER CORD LENGTH	4.5 ft
AC ADAPTER	Input: 100-240V, 50/60Hz, 0.5A; Output: 5V, 2A, 5 ft.
BTUS	20.8 BTU/Hr
MAX SUPPORTED VIDEO RESOLUTION	3840 x 2160 (4K) @ 60Hz
LED INDICATORS	(x3) Orange (Monitor Signal); (x1) Green (Power)
OPERATING TEMPERATURE RANGE	14° to 167°F (10° to 75°C)
STORAGE TEMPERATURE RANGE	-4° to 176°F (-20° to 80°C)
NUMBER OF PORTS	3
POWER CONSUMPTION	6.1 W
MAX RESOLUTION	4K/60
TAA COMPLIANCE	Yes
INPUT X OUTPUT	1 x 3
