



Eaton CS16USBW

Multi-Device Charging Station, 16 USB Ports,
iPad and Android Tablets, Wall-Mount
Option, White

□□□□

PRODUCT NAME	Eaton Tripp Lite series stationary charging station
CATALOG NUMBER	CS16USBW
UPC	037332188946
PRODUCT LENGTH/DEPTH	17.72 in
PRODUCT HEIGHT	14.57 in
PRODUCT WIDTH	23.62 in
PRODUCT WEIGHT	56.18 lb
WARRANTY	2 year limited
COMPLIANCES	CE Marked EIA-310-E FCC Class B RoHS REACH
CERTIFICATIONS	NOM UL 60950-1

□□□□	
FREQUENCY RATING	50/60 Hz 50 / 60 Hz (auto-select)
CHARGING PORTS DETAILS	Pass through
NUMBER OF CHARGING PORTS	16
TOTAL CHARGING AMPS	40A
PRODUCT TYPE	Multi-Device Charger
FEATURES	Flex Center
DEVICE COMPATIBILITY	Tablet Phone
FREQUENCY COMPATABILITY	50/60 Hz
COLOR	White
INPUT PLUG TYPE	NEMA 5-15P
MATERIAL	Steel
CHARGING PORTS / AMPS	2.4A
INPUT CORD LENGTH	10 ft
INPUT FREQUENCY	50 / 60 Hz (auto-select)
CHARGING METHOD	USB
INPUT NOMINAL VOLTAGE	230 VAC 120 VAC
PRODUCT FEATURES	Flow-Through Ventilation Overcurrent Protection Overcharge Protection EMI/RFI Line Noise Protection Built-In Circuit Breaker Cord Management Locking
PACKAGE CONTENTS	Owner's manual CS16USBW 16-Device USB Charging Station Cabinet, White Detachable 10-ft. (3.05 m) AC input cord w/NEMA 5-15P plug (2) Keys
PRODUCT HIGHLIGHTS	Adjustable device dividers and integrated cord management 2-year limited warranty (Worldwide) Detachable 10-ft. (3.05 m) power cord Locking steel cabinet with flow-through ventilation Ships fully assembled and mounts to wall, desk, table

	or floor Fast 2.4A USB charging, syncing and storage for 16 tablets
CHARGING FORM FACTOR	Stationary cabinet
CHARGING PORT TYPE	USB A (FEMALE)
DEVICE SLOTS	16
NUMBER OF SHELVES	1
POWER CONSUMPTION	56 W
VOLTAGE COMPATIBILITY (VAC)	110 - 240 VAC
CHARGING STATION FORM FACTOR	Stationary cabinet
CHARGING AMPS PER PORT	2.4 A 2.4A
CHARGER FUNCTION	Charge Secure Sync
LOCK	Key

□□□□:
□□□□:
□□□:
□□: