



Eaton CS48USB

Multi-Device Charging Station, 48 USB Ports,
iPad and Android Tablets, Black

□□□□

PRODUCT NAME	Eaton Tripp Lite series stationary charging station
CATALOG NUMBER	CS48USB
UPC	037332185433
PRODUCT LENGTH/DEPTH	21.57 in
PRODUCT HEIGHT	35.63 in
PRODUCT WIDTH	23.62 in
PRODUCT WEIGHT	149.95 lb
WARRANTY	2 year limited
COMPLIANCES	FCC Class B CE Marked EIA-310-E REACH RoHS
CERTIFICATIONS	UL 60950-1 NOM

CS48USB		CS48USB	
FREQUENCY RATING	50/60 Hz 50 / 60 Hz (auto-select)		
CHARGING PORTS DETAILS	Pass through		
NUMBER OF CHARGING PORTS	48		
TOTAL CHARGING AMPS	120A		
TOTAL CHARGING WATTS	600		
PRODUCT TYPE	Multi-Device Charger		
FEATURES	Flex Center		
DEVICE COMPATIBILITY	Phone Tablet		
FREQUENCY COMPATABILITY	50/60 Hz		
COLOR	Black		
INPUT PLUG TYPE	NEMA 5-15P		
MATERIAL	Steel		
CHARGING PORTS / AMPS	2.4A		
INPUT CORD LENGTH	10 ft		
INPUT FREQUENCY	50 / 60 Hz (auto-select)		
CHARGING METHOD	USB		
INPUT NOMINAL VOLTAGE	230 VAC 120 VAC		
PRODUCT FEATURES	Built-In Circuit Breaker Cord Management Locking Overcharge Protection Overcurrent Protection EMI/RFI Line Noise Protection Flow-Through Ventilation		
PACKAGE CONTENTS	Owner's manual Detachable AC input cord with NEMA 5-15P plug, 10 ft. (3.1 m) (2) Keys CS48USB Multi-Device Charging Station, Black		
PRODUCT HIGHLIGHTS	Supports charging of iPad, Android, Surface, Kindle and other USB tablets Sturdy steel construction with locking doors that help prevent theft or tampering 10 ft. cord with NEMA 5-15P plug allows great flexibility in reaching AC outlets		

	48 internal USB ports provide up to 2.4A apiece for fast charging of tablets 2-year limited warranty (Worldwide) Flow-through ventilation helps prevent connected tablets from overheating
CHARGING FORM FACTOR	Stationary cabinet
CHARGING PORT TYPE	USB A (FEMALE)
DEVICE SLOTS	48
NUMBER OF SHELVES	3
POWER CONSUMPTION	224 W
VOLTAGE COMPATIBILITY (VAC)	110 - 240 VAC
CHARGING STATION FORM FACTOR	Stationary cabinet
CHARGING AMPS PER PORT	2.4 A 2.4A
LOCK	Key

□□□□:
□□□□:
□□□:
□□: