



□□□□

Eaton CSM01893

CSM01893MATSN-400/200/4HIII-EN

□□□□

PRODUCT NAME	Eaton MATSN automatic transfer switch
CATALOG NUMBER	CSM01893
PRODUCT LENGTH/DEPTH	180 mm
PRODUCT HEIGHT	430 mm
PRODUCT WIDTH	498 mm
PRODUCT WEIGHT	15.1 kg
CERTIFICATIONS	CE CB

□□□□

□□

NOMINAL INPUT VOLTAGE	400 V
FREQUENCY RATING	50/60 Hz
INPUT VOLTAGE - MIN	400 V
INPUT VOLTAGE - MAX	400 V
NOMINAL INPUT CURRENT SHORE	200 A
TRANSFER TIME SWITCH ON - MIN	0 ms
TRANSFER TIME SWITCH ON - MAX	100 ms
TRANSFER TIME SWITCH OFF - MIN	0 ms
TRANSFER TIME SWITCH OFF - MAX	100 ms
AMBIENT TEMPERATURE - MIN	-20 °C
AMBIENT TEMPERATURE - MAX	55 °C
NUMBER OF POLES	Four-pole
CONTROLLER TYPE	Type H Separate controller
NUMBER OF POSITIONS	3
RATED CURRENT	200 A
RATED INSULATION VOLTAGE	1000 V
RATED IMPULSE WITHSTAND VOLTAGE UIMP	12 kV
RATED OPERATIONAL VOLTAGE UE AT 50/60HZ	400 V
POLLUTION DEGREE	3
WIRING METHOD	Front panel wiring
FRAME SIZE	3
RATED SHORT TIME MAKING CAPACITY ICM	25.55 kA
UTILIZATION CATEGORY	AC-33iB AC-33B AC-33iA



© 2026 〇〇 〇〇〇〇〇〇〇〇