


Eaton FT2SE400ATL18

Eaton FlexiTech, Safety Escape Route, 400lm, AT, MNM (L'), 1 to 8H

PRODUCT NAME	Eaton FlexiTech SE SC emergency luminaire
CATALOG NUMBER	FT2SE400ATL18
PRODUCT LENGTH/DEPTH	228 mm
PRODUCT HEIGHT	31 mm
PRODUCT WIDTH	120 mm
PRODUCT WEIGHT	0.4 kg
WARRANTY	Refer to warranty document.
CERTIFICATIONS	CE

BATTERY VOLTAGE	3.2 V
BATTERY NUMBER OF CELLS	2
BATTERY QUALITY	Lithium-ion
GLOW WIRE TEST	850 °C
PERMISSIBLE AMBIENT TEMPERATURE - MIN	0 °C
PERMISSIBLE AMBIENT TEMPERATURE - MAX	45 °C
PROTECTION CLASS	II
OUTDOOR USE COMPLIANCE	False
EXPLOSION PROTECTED	False
DEGREE OF PROTECTION	IP43
MODE	Maintained / Non-Maintained (M / NM)
LAMP TYPE	LED not exchangeable
WITH LIGHT SOURCE	True
LAMP HOLDER	None
MONITORING EQUIPMENT	Automatic self test
POWER SUPPLY SYSTEM	Peripheral (individual battery)
VOLTAGE TYPE	AC
APPARENT POWER AT MAINS OPERATION	5 VA
POWER FACTOR	0.4
WIRING SYSTEM	Continuous circuit/emergency circuit
WITH REMOTE SWITCH CONNECTION	False
RESERVE-POLARITY PROTECTED	True
ENERGY EFFICIENCY CLASS	A++, A+, A (LED)
CONDUCTOR CROSS SECTION	2.5
CONNECTION TYPE	Plug-in connection
MAX. SYSTEM POWER	2 W
TYPE OF CONTROL GEAR	LED operating device current-controlled
TYPE OF WIRING	Through wiring included
NOMINAL VOLTAGE AC - MAX	230 V
NOMINAL VOLTAGE AC - MIN	230 V
RATED AMBIENT TEMP ACC. IEC62722-2-1 - MIN	5 °C
RATED AMBIENT TEMP ACC. IEC62722-2-1 - MAX	45 °C
NOMINAL OPERATION TIME - MIN	1 hour



NOMINAL OPERATION TIME - MAX	8 hour
AUTONOMY	1/8 hours
MOUNTING METHOD	Ceiling surface mounting
MATERIAL HOUSING	Plastic
COLOR HOUSING	White
MATERIAL COVER	Plastic, transparent
PICTOGRAM INCLUDED	False
BUILT-IN LENGTH	245 mm
BUILT-IN WIDTH	130 mm
BUILT-IN HEIGHT/DEPTH	50 mm
NUMBER OF POLES (NUMERIC)	3
IMPACT STRENGTH	IK07
KIND OF LUMINAIRE	Safety luminaire for escape route and open area lighting
RATED LUMINOUS FLUX ACC. IEC 62722-2-1	400 lm
COLOR TEMPERATURE - MAX	6500 K
COLOR TEMPERATURE - MIN	6500 K
LIGHT DISTRIBUTOR	Focal lens
ENERGY EFFICIENCY CLASS OF THE BUILT-IN LAMP	A++, A+, A (LED)
FUNCTION	Escape route lighting
COLOR OF LIGHT	White
COLOR RENDERING INDEX (CRI)	70
LUMINOUS FLUX IN STANDBY MODE	100 lm
NUMBER OF LIGHTING HEADS	1
SUITABLE FOR NUMBER OF LAMPS	1
DATA CONNECTION TERMINAL	0.5 - 2.5 mm ²
FREQUENCY	50/60 Hz
MAIN CONNECTION TERMINAL	0.5 - 2.5mm ²
NUMBER OF LEDS	36
SHAPE	Rectangular
TOTAL LENGTH	228 mm
APPLICATION	Other
TESTING SYSTEM	Auto-Test

:
:
:
: