

Eaton N232-100-FTP

Cat6 RJ45 Pass-Through FTP Modular Plug, 100 Pack

PRODUCT NAME	Eaton Tripp Lite series copper plug
CATALOG NUMBER	N232-100-FTP
UPC	037332260727
PRODUCT LENGTH/DEPTH	9.5 in
PRODUCT HEIGHT	1.75 in
PRODUCT WIDTH	7 in
PRODUCT WEIGHT	0.485 lb
WARRANTY	Limited lifetime
COMPLIANCES	TAA Compliant

TYPE	RJ45 Plug
PACKAGE CONTENTS	(100) Cat6 RJ45 pass-through FTP modular plugs
SYSTEM REQUIREMENTS	Cat6a Cat6
PRODUCT FEATURES	TAA Compliant
PRODUCT HIGHLIGHTS	Work with most RJ45 crimping tools and 24-26 AWG FTP and F/UTP Cat6 cables Staggered nose pattern reduces near-end crosstalk for clearer transmission Ideal for use with solid or stranded conductor Cat6 cable in your Ethernet application 100 Cat6 RJ45 pass-through FTP modular plugs in an easy-to-pack plastic bag Lifetime limited warranty (Worldwide) Shields against disruptive EMI/RFI noise that can inflict hardware damage or data loss
TECHNOLOGY	Cat6a Cat6
FEATURES	Flex Center
OPERATING TEMPERATURE RANGE	-40° to 185°F (-40° to 85°C)
RELATIVE HUMIDITY	15% to 65% RH, Non-Condensing
STORAGE HUMIDITY RANGE	41° to 86°F (5° to 30°C)
STORAGE TEMPERATURE	41° to 86°F (5° to 30°C)
AWG-SIZE	24 - 26
OUTER CABLE DIAMETER	< 6.2 mm
OPERATING TEMPERATURE	-40° to 185°F (-40° to 85°C)
TAA COMPLIANCE	Yes
CABLE SHEATH MATERIAL	FTP



:
:
:
: